

Grounding Clamp

By ANDERSON  
Catalog # [GC1117D](#)

"Grounding Clamp, Bronze Bolted, Copper Two Parallel Cables to Rod or Tube Perpendicular, U-bolt style, Cables Range 0.365"-0.575" dia. to 5/8"-1" OD Rod or 3/8"-3/4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



\*Representative Image

Features

- "Everdur hardware supplied by adding Suffix ED"

General

EU RoHS Indicator	No
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359306108

Dimensions

Diameter - Clamping Hardware	2 in
Diameter - Rod / Tube	2 in
Diameter - Rod / Tube Outside	2.5 in
Weight	2.744 lb

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.574 in
Conductor Diameter Range	0.574 - 0.813
Conductor Type	Copper

Product Assets

- [Sales Drawings - C-2951 \(GC111 Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)

