


Grounding Clamp

By ANDERSON
Catalog # [GC1118C](#)

"Grounding Clamp, Bronze Bolted, Copper Two Parallel Cables to Rod or Tube Perpendicular, U-bolt style, Cables Range 0.204"-0.419" dia. to 1-3/4" OD Rod or 1-1/4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



*Representative Image

Features

- "Everdur hardware supplied by adding Suffix ED"

General

Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359306122

Dimensions

Diameter - Clamping Hardware	2.5 in
Diameter - Rod / Tube	2.5 in
Diameter - Rod / Tube Outside	3 in
Weight	2.352 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

Logistics

Pallet Quantity	648
-----------------	-----

Product Assets

[Catalogs - Substation Connectors Combined \(CA05044E\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)