

Grounding Clamp

By ANDERSON
Catalog # [GC140G3](#)

bronze alloy ground clamp for clamping a copper cable to a flat bar



*Representative Image

Features

- "Everdur hardware supplied by adding Suffix ED
- If longer bolts are required, add bar thickness to catalog number. Example: GC140G312 for 1/2" bar"

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GC140G3
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Galvanized Steel
Material - Hardware	Galvanized Steel
UPC	096359400752

Dimensions

Weight	0.686 lb
--------	----------

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.629 in
Conductor Diameter Range	0.629 - 0.813
Conductor Type	Copper

Product Assets

- [Sales Drawings - C-2705 \(GC140 Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)