

Grounding Clamp

By ANDERSON
Catalog # [GC141AG212](#)

Grounding Clamp, Galv-Steel Bolted, Copper Cable to Flat,
Cable #4 Sol-300 MCM (0.204"-0.630" dia.) to 1/2" Thick Flat,
Two piece Clamp, Material: Casting-Bronze alloy, Hardware-
Galvanized steel 1/2" Bolt, Nut & Split-Lock-Washer



*Representative Image

Features

- Bolts furnished are for clamping to 1/4" flat bar
- Everdur hardware supplied by adding Suffix ED

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Galvanized Steel
Material - Hardware	Galvanized Steel
UPC	096359306740

Dimensions

Diameter - Clamping Hardware	0.5 in
Weight	0.490 lb

Conductor Related

Conductor Diameter - Maximum	0.63 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.63
Conductor Type	Copper

Logistics

Pallet Quantity	4000
-----------------	------

Product Assets

[Sales Drawings - C-2564 \(AGC and GC141 Product Families\)](#)

[Technical Solutions - AN-GC141AG212-SPEC-EN](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)