

## Grounding Clamp

By ANDERSON  
Catalog # [GC141AG2TP](#)

Grounding Clamp, Galv-Steel Bolted, Copper Cable to Flat, Cable #4 Sol-300 MCM (0.204"-0.630" dia.) to 1/4" Thick Flat, Two piece Clamp, Material: Casting-Bronze alloy w/ Tin Plating, Hardware-Galvanized steel 1/2" Bolt, Nut & Split-Lock-Washer



\*Representative Image

### Features

- Bolts furnished are for clamping to 1/4" flat bar
- Everdur hardware supplied by adding Suffix ED
- TP suffix adds Tin Plating to the body and cap
- If longer bolts are required, add bar thickness to catalog number. Example: GC141AG212 for 1/2" bar

### General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Galvanized Steel
Material - Hardware	Galvanized Steel
UPC	096359306788

### Dimensions

Diameter - Clamping Hardware	0.5 in
Weight	0.490 lb

### Conductor Related

Conductor Diameter - Maximum	0.63 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.63
Conductor Type	Copper

### Product Assets

[Sales Drawings - C-2564 \(AGC and GC141 Product Families\)](#)  
[Technical Solutions - AN-GC141AG2TP-SPEC-EN](#)  
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)  
[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)