

Grounding Clamp

By ANDERSON
Catalog # [GC141G3](#)

Grounding Clamp, Galv-Steel Bolted, Copper Cable to Flat, Cable 300-500 MCM (0.629"-0.813" dia.) to 1/4" Thick Flat, Two piece Clamp, Material: Casting-Bronze alloy, Hardware-Galvanized steel 1/2" Bolt, Nut & Split-Lock-Washer



*Representative Image

Features

- Bolts furnished are for clamping to 1/4" flat bar
- Everdur hardware supplied by adding Suffix ED
- If longer bolts are required, add bar thickness to catalog number. Example: GC141G312 for 1/2" bar

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Galvanized Steel
Material - Hardware	Galvanized Steel
UPC	096359306832

Dimensions

Weight	0.392 lb
--------	----------

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.629 in
Conductor Diameter Range	0.629 - 0.813
Conductor Type	Copper

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Sales Drawings - C-2564 \(AGC and GC141 Product Families\)](#)
[Technical Solutions - AN-GC141G3-SPEC-EN](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)