

Automatic Splice, Full Tension, for 1/4"

By ANDERSON
Catalog # GLS5000

Automatic Splice, Full Tension, for 1/4" HS, Common, Utilities,
Siemens-Martin guy grades



*Representative Image

Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Catalog Number	GLS5000
Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359363521

Dimensions

Dimensions	6.400 in x 0.900 in x 0.900 in
Height	0.9 in
Length	6.4 in
Weight	0.657 lb
Width	0.9 in

Conductor Related

Conductor Diameter - Maximum	0.231 in
Conductor Diameter - Minimum	0.249 in
Conductor Diameter Range	0.249 - 0.231

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	7200
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Communication Connectors - Deadends and Splices](#)
- [Sales Drawings - GLS500X_sales_drawing](#)
- [Specifications - GLS5000](#)