

Automatic Splice, Full Tension, for
5/16"

By ANDERSON
Catalog # [GLS5001](#)

Automatic Splice, Full Tension, for 5/16" HS, Common, Utilities,
Siemens-Martin guy grades



*Representative Image

Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Catalog Number	GLS5001
Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359363538

Dimensions

Dimensions	7.400 in x 1.100 in x 1.100 in
Height	1.1 in
Length	7.4 in
Weight	0.657 lb
Width	1.1 in

Conductor Related

Conductor Diameter - Maximum	0.324 in
Conductor Diameter - Minimum	0.3 in
Conductor Diameter Range	0.300 - 0.324

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	2000
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Communication Connectors - Deadends and Splices](#)
- [Sales Drawings - GLS500X_sales_drawing](#)
- [Specifications - GLS5001](#)