

**Automatic Splice, Full Tension, for
1/4" EHS, AW**

By ANDERSON
Catalog # [GLS5040](#)

Automatic Splice, Full Tension, for 1/4" Alumoweld, HS,
Common, Utilities, Siemens-Martin guy grades



Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359389477

Dimensions

Dimensions	8.300 in x 1.130 in x 1.130 in
Height	1.13 in
Length	8.3 in
Weight	0.65 lb
Width	1.13 in

Conductor Related

Conductor Diameter - Maximum	0.249 in
Conductor Diameter - Minimum	0.231 in
Conductor Diameter Range	0.231 - 0.249

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	3600
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Sales Drawings - GLS5xxx_sales_drawing](#)