

## Automatic Splice, Full Tension, for 1/4" EHS, AW

By ANDERSON  
Catalog # GLS5040



Automatic Splice, Full Tension, for 1/4" Alumoweld, HS,  
Common, Utilities, Siemens-Martin guy grades

\*Representative Image

### Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

### General

Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359389477

### Dimensions

Dimensions	8.300 in x 1.130 in x 1.130 in
Height	1.130 in
Length	8.300 in
Weight	0.650 lb
Width	1.130 in

### Conductor Related

Conductor Diameter - Maximum	0.249 in
Conductor Diameter - Minimum	0.231 in
Conductor Diameter Range	0.231 - 0.249

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	3600
-----------------	------

### Product Assets

[Catalogs - Communication Connectors - Deadends and Splices](#)  
[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - GLS5xxx\\_sales\\_drawing](#)  
[Technical Solutions - AN-GLS5040-SPEC-EN](#)