

Automatic Splice, Full Tension, for 5/16" EHS, AW

By ANDERSON
Catalog # GLS5041



Automatic Splice, Full Tension, for 5/16" Alumoweld, HS,
Common, Utilities, Siemens-Martin guy grades

*Representative Image

Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359389484

Dimensions

Dimensions	9.400 in x 1.220 in x 1.220 in
Height	1.220 in
Length	9.400 in
Weight	0.776 lb
Width	1.220 in

Conductor Related

Conductor Diameter - Maximum	0.324 in
Conductor Diameter - Minimum	0.300 in
Conductor Diameter Range	0.300 - 0.324

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	2400
-----------------	------

Product Assets

[Catalogs - Communication Connectors - Deadends and Splices](#)
[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - GLS5xxx_sales_drawing](#)
[Technical Solutions - AN-GLS5041-SPEC-EN](#)