

Automatic Splice, Full Tension, for 3/8" EHS, AW, AWAC

By ANDERSON
Catalog # [GLS5042](#)



Automatic Splice, Full Tension, for 3/8" Alumoweld HS,
Common, Utilities, Siemens-Martin guy grades

*Representative Image

Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359389491

Dimensions

Dimensions	10.000 in x 1.480 in x 1.480 in
Height	1.480 in
Length	10.000 in
Weight	1.207 lb
Width	1.480 in

Conductor Related

Conductor Diameter - Maximum	0.372 in
Conductor Diameter - Minimum	0.348 in
Conductor Diameter Range	0.348 - 0.372

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1600
-----------------	------

Product Assets

[Catalogs - Communication Connectors - Deadends and Splices](#)
[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - GLS5xxx_sales_drawing](#)
[Technical Solutions - AN-GLS5042-SPEC-EN](#)