

HUBBELL

Power Systems

Automatic Splice, Full Tension, for 7/16" EHS, AW, AWAC

By ANDERSON
Catalog # [GLS5043](#)



Automatic Splice, Full Tension, for 7/16" Alumoweld HS,
Common, Utilities, Siemens-Martin guy grades

*Representative Image

Features

- Individually bagged to seal out dirt before use
- GLS Automatic splices will hold a minimum of 90% of the guy wire breaking strength

General

Catalog Number	GLS5043
Color Code	None
Material	Aluminum Alloy; Steel
Material - Gripping Unit	Plated Steel
UPC	096359389507

Dimensions

Dimensions	11.000 in x 1.600 in x 1.600 in
Height	1.6 in
Length	11 in
Weight	1.571 lb
Width	1.6 in

Conductor Related

Conductor Diameter - Maximum	0.459 in
Conductor Diameter - Minimum	0.402 in
Conductor Diameter Range	0.402 - 0.459

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Catalogs - Communication Connectors - Deadends and Splices](#)
[Sales Drawings - GLS5xxx_sales_drawing](#)



A Hubbell brand