

HUBBELL

Power Systems

Transformer Tank Grounding Clamp, #8Sol. - 2/0 Str

By ANDERSON
Catalog # [GTCS34A](#)

Grounding Clamp, Copper Cable to Transformer Tank, Hex wrench shoulder.



*Representative Image

Features

- Bronze alloy ground clamp for tapping copper conductor to transformer tank
- Tapered thread at base of stud ensures positive locking and electrical contact without lockwashers.
- Hex wrenching surface above tapered thread provides easy installation.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GTCS34A
Material - Body	Bronze
Material - Eyebolt	Bronze
Material - Hardware	Stainless Steel
Material - Hex Nut	Stainless Steel
Material - Washer	Stainless Steel
Number of Eyebolts	1
Number of Stud Threads	13
Style	Eyebolt
UPC	096359313823

Dimensions

Diameter - Stud	0.5 in
Dimensions	2.000 in x 1.201 in x 1.976 in
Height	1.976 in
Length	2 in
Messenger Diameter Range	0 - 0
Weight	0.294 lb
Width	1.201 in

Conductor Related

Conductor Diameter (Ground Tap) - Maximum	0 in
Conductor Diameter (Ground Tap) - Minimum	0 in
Conductor Diameter (Ground Tap) Range	0 - 0
Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.128 in
Conductor Diameter Range	0.128 - 0.419
Conductor Type	Copper
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Logistics

Pallet Quantity	8000
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - C-9822](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-GTCS34A-SPEC-EN | REV 6/2024