

## Transformer Tank Grounding Clamp, #8Sol. - 2/0 Str, Tin Plated

By ANDERSON  
Catalog # [GTCS34ATP](#)

Grounding Clamp, Copper Cable to Transformer Tank, Hex  
wrench shoulder, Tin Plated.



\*Representative Image

### Features

- 2 position eyebolt allows parallel or perpendicular conductor installation.

### General

Cover Available	No
Inhibitor Loaded	No
Material	Bronze; Copper
Material - Body	Bronze Alloy
Material - Eyebolt	Silicon Bronze
Material - Hardware	Silicon Bronze or Stainless Steel
Number of Stud Threads	13
Product Category	Mechanical Connectors
Style	2 Position Eye Bolt
UPC	096359313830

### Dimensions

Bolt Diameter	0.380 in
Diameter - Bolt	0.38 in
Diameter - Stud	0.5 in
Dimensions	2.000 in x 1.201 in x 1.976 in
Height	1.976 in
Length	2.000 in
Weight	0.294 lb
Width	1.201 in

### Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.128 in
Conductor Diameter Range	0.128 - 0.419

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Carton Quantity	100
-----------------	-----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - C-9822](#)  
[Technical Solutions - AN-GTCS34ATP-SPEC-EN](#)

### Related Products

[GTCS34A - Transformer Tank Grounding Clamp, #8Sol. - 2/0 Str](#)