

HUBBELL

Power Systems

Transformer Tank Grounding Clamp, #6Sol. - 250 MCM

By ANDERSON
Catalog # [GTCS41](#)

Grounding Clamp, Copper Cable to Transformer Tank, Hex wrench shoulder.



*Representative Image

Features

- Bronze alloy ground clamp for tapping copper conductor to transformer tank
- Tapered thread at base of stud ensures positive locking and electrical contact without lockwashers.
- Hex wrenching surface above tapered thread provides easy installation.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GTCS41
Material - Body	Bronze
Material - Eyebolt	Bronze
Material - Hardware	Stainless Steel
Material - Hex Nut	Stainless Steel
Material - Washer	Stainless Steel
Number of Eyebolts	1
Number of Stud Threads	13
Style	Eyebolt
UPC	096359313854

Dimensions

Diameter - Stud	0.5 in
Dimensions	2.500 in x 1.625 in x 2.620 in
Height	2.62 in
Length	2.5 in
Messenger Diameter Range	0 - 0
Weight	0.588 lb
Width	1.625 in

Conductor Related

Conductor Diameter (Ground Tap) - Maximum	0 in
Conductor Diameter (Ground Tap) - Minimum	0 in
Conductor Diameter (Ground Tap) Range	0 - 0
Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.575
Conductor Type	Copper
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Logistics

Pallet Quantity	4000
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - C-9822](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-GTCS41-SPEC-EN | REV 6/2024