

Transformer Tank Grounding Clamp, #6Sol. - 250 MCM, Tin Plated

By ANDERSON
Catalog # [GTCS41TP](#)

Grounding Clamp, Copper Cable to Transformer Tank, Hex
wrench shoulder, Tin Plated.



*Representative Image

Features

- 2 position eyebolt allows parallel or perpendicular conductor installation.

General

Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze; Copper
Material - Body	Bronze Alloy
Material - Eyebolt	Silicon Bronze
Material - Hardware	Silicon Bronze or Stainless Steel
Number of Stud Threads	13
Product Category	Mechanical Connectors
Style	2 Position Eye Bolt
UPC	096359313861

Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Diameter - Stud	0.5 in
Weight	0.588 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.575

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	4000
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Technical Solutions - AN-GTCS41TP-SPEC-EN](#)

Related Products

[GTCS41 - Transformer Tank Grounding Clamp, #6Sol. - 250 MCM](#)
[GTCS41TP - Transformer Tank Grounding Clamp, #6Sol. - 250 MCM, Tin Plated](#)