

Suspension Clamp

By ANDERSON
Catalog # [HAS204N](#)



The HAS suspension clamp is a saddle type suspension clamp designed for use on standard voltage transmission lines. The HAS clamps are designed for use with all aluminum, ACSR, or aluminum alloy conductor. Material: Clamp-Aluminum alloy, Socket-Galvanized Ductile iron. Clamping Range: 0.400-0.850

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter"

General

Bolt Installation Torque (Recommended)	480 in-lbs
Catalog Number	HAS204N
EU RoHS Indicator	No
Fitting Type	None
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Suspension Clamp
Strength Rating - Ultimate	25000 lb
Body Type	Standard Voltage Suspension Clamps
U-Bolts	1/2 in
UPC	096359315056

Dimensions

Angle - Take-Off Maximum	20.5 °
Clamping - Maximum	2.04 in
Clamping - Minimum	1.4 in
Clevis Opening	2.6875 in
Diameter - Clevis Pin	0.625 in
Height	3.53125 in
Length	10.5 in
Weight	4.9 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	1.4- 2.04
Conductor Compatibility	ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-

30/7;ACSR-Peacock-605-
24/7;ACSR-Squab-605-
26/7;ACSR-Teal-605-
30/19;ACSR-Kingbird-636-
18/1;ACSR-Swift-636-
36/1;ACSR-Rook-636-
24/7;ACSR-Grosbeak-636-
26/7;ACSR-Egret-636-
30/19;ACSR-Flamingo-666.6-
24/7;ACSR-Gannet-666.6-
26/7;ACSR-Stilt-715.5-
24/7;ACSR-Starling-715.5-
26/7;ACSR-Redwing-715.5-
30/19;ACSR-Coot-795-
36/1;ACSR-Cuckoo-795-
24/7;ACSR-Drake-795-
26/7;ACSR-Tern-795-
45/7;ACSR-Condor-795-
54/7;ACSR-Mallard-795-
30/19;ACSR-Ruddy-900-
45/7;ACSR-Canary-900-
54/7;ACSR-Rail-954-
45/7;ACSR-Cardinal-954-
54/7;ACSR-Ortolan-1033.5-
45/7;ACSR-Curlew-1033.5-
54/7;ACSR-Bluejay-1113-
45/7;ACSR-Finch-1113-
54/19;ACSR-Bunting-1192.5-
45/7;ACSR-Martin-1351.5-
54/19;ACSR-Bobolink-1431-
45/7;ACSR-Plover-1431-
54/19;ACSR-Nuthatch-1510.5-
45/7;ACSR-Parrot-1510.5-
54/19;ACSR-Lapwing-1590-
45/7;ACSR-Falcon-1590-
54/19;ACSR-Chukar-1780-
84/19;ACSR-Bluebird-2156-
84/19;ACSR-Kiwi-2167-
72/7;ACSR-Thrasher-2312-
76/19;ACSR-Joree-2515-
76/19;AAC-Orchid-636-
37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-

Nasturtium-715.5-61;AAC-	30/7;ACAR-1109-30/7;ACAR-
Cattail-750-61;AAC-Arbutus-	1172-30/7;ACAR-1172-
795-37;AAC-Lilac-795-61;AAC-	18/19;ACAR-1933-42/19;ACAR-
Cockscomb-900-37;AAC-	2493-72/19;ACAR-2493-54/37
Snapdragon-900-61;AAC-	
Magnolia-954-37;AAC-	
Goldenrod-954-61;AAC-	
Camellia-1000-61;AAC-	
Bluebell-1033.5-37;AAC-	
Larkspur-1033.5-61;AAC-	
Marigold-1113-61;AAC-	
Hawthorn-1192.5-61;AAC-	
Narcissus-1272-61;AAC-	
Gladiolus-1510.5-61;AAC-	
Coreopsis-1590-61;AAC-	
Cowslip-2000-91;AAC-Lupine-	
2500-91;ACAR-653.1-	
12/7;ACAR-739.8-18/19;ACAR-	
853.7-30/7;ACAR-1024.5-	

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	180
-----------------	-----

Product Assets

- [Catalogs - Transmission Connectors Catalog - Full](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - HAS Product Family](#)
- [Specifications - HAS204N](#)



A Hubbell brand