

Hot Line Link, Clevis Ball

By ANDERSON
Catalog # [HBC50L](#)

"Hot Line Oval-Eye Ball, Forged Steel, Oval Eye: 0.938" x 2.125"
Opening x 0.688" Thick, UTS 30,000 lb"



Features

- "For use with ANSI class 52-8 & 52-11 insulators
- Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-24" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicableExample: HBC5012D5 for 12.500" length
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Extension Link Type	Clevis Ball
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Strength Rating - Ultimate	50000 lb

Dimensions

Insulator Throat Diameter 0 - 0
Range

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Technical Solutions - AN-HBC50L-SPEC-EN](#)