

Hot Line Link, Clevis Eye

By ANDERSON
Catalog # [HCE1000613](#)

"Hot Line Oval-Eye Oval-Eye, Rotated, Oval Eye: 0.938" x 2.375" x 0.750" Thick, UTS 40,000 lb"



*Representative Image

Features

- "Material: Body-Ductile Iron, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Coupling Orientation	Straight
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Series	HCE Series
Strength Rating - Ultimate	30000 lb
UPC	096359315568

Dimensions

Diameter - Eye Hole	0.813 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	10 in
Weight	3.038 lb

Logistics

Pallet Quantity	405
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Technical Solutions - AN-HCE1000613-SPEC-EN](#)