

HUBBELL Power Systems

Compression Stirrup

By ANDERSON
Catalog # [HLS22P](#)

Aluminum Overhead Compression Stirrup



*Representative Image

Features

Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	HLS22P
Compression Tool Type	O die
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316428

Dimensions

Copper Loop Size	0.258 in
Diameter - Stirrup Nominal Wire	#2 Solid
Height	3.25 in
Weight	0.49 lb
Width - Main Contact	4 in

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;AAC-Iris-2-7;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter - Maximum	0.325
Conductor Diameter - Minimum	0.25
Conductor Diameter Range	0.25 - 0.325
Conductor Type	Aluminum

Logistics

Packaging Type Bag

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - CC-19211](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-HLS22P-SPEC-EN | REV 6/2024