

# HUBBELL Power Systems

## Compression Stirrup

By ANDERSON  
Catalog # [HLS3502P](#)

Aluminum Overhead Compression Stirrup



\*Representative Image

### Features

Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	HLS3502P
Compression Tool Type	EEl-13A, 1-1/8
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316466

### Dimensions

Copper Loop Size	0.258 in
Diameter - Stirrup Nominal Wire	#2 Solid
Height	3.25 in
Weight	0.157 lb
Width - Main Contact	4 in

### Conductor Related

Conductor Compatibility	ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Brahma-203.2-16/19;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Daffodil-350-19
Conductor Diameter - Maximum	0.721
Conductor Diameter - Minimum	0.607
Conductor Diameter Range	0.607 - 0.721
Conductor Type	Aluminum

### Logistics

Packaging Type	Bag
Pallet Quantity	750

### Product Assets

[Catalogs - Distribution Connectors](#)  
[Sales Drawings - CC-19211](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HLS3502P-SPEC-EN | REV 6/2024