

HUBBELL Power Systems

Compression Stirrup

By ANDERSON

Catalog # [HLS65010P](#)

Aluminum Overhead Compression Stirrup



*Representative Image

Features

Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	HLS65010P
Compression Tool Type	1-1/2
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316497

Dimensions

Copper Loop Size	0.325 in
Diameter - Stirrup Nominal Wire	1/0 Solid
Height	3.75 in
Weight	0.98 lb
Width - Main Contact	4 in

Conductor Related

Conductor Compatibility	ACSR-Pigeon-3/0-6/1;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;AAC-Oxlip-4/0-7;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAAC 6201 Alloy-Amherst-195.7-6/18
Conductor Diameter - Maximum	0.93
Conductor Diameter - Minimum	0.811
Conductor Diameter Range	0.811 - 0.93
Conductor Type	Aluminum

Logistics

Carton Quantity	25
Packaging Type	Bag

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - CC-19211](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-HLS65010P-SPEC-EN | REV 6/2024