

# HUBBELL Power Systems

## Compression Stirrup

By ANDERSON

Catalog # [HLS80020P](#)

Aluminum Overhead Compression Stirrup



\*Representative Image

### Features

Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	HLS80020P
Compression Tool Type	1-1/2
EU RoHS Indicator	No
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316534

### Dimensions

Copper Loop Size	0.365 in
Diameter - Stirrup Nominal Wire	2/0 Solid
Height	3.75 in
Weight	0.98 lb
Width - Main Contact	4 in

### Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Coot-795-36/1;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61
Conductor Diameter - Maximum	1.04
Conductor Diameter - Minimum	0.93
Conductor Diameter Range	0.93 - 1.04
Conductor Type	Aluminum

### Logistics

Packaging Type	Bag
Pallet Quantity	450

### Product Assets

[Catalogs - Distribution Connectors](#)  
[Sales Drawings - CC-19211](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HLS80020P-SPEC-EN | REV 6/2024