

Hot Line Link, Oval-Eye Ball

By ANDERSON
Catalog # [HOEB30L](#)

"Hot Line Link, Socket Eye. Eye: 0.500" Thick. With 0.690" Dia. Hole UTS 30,000 lb"



Features

- "For use with ANSI class 52-3 & 52-5 insulators
- Material: Body-Galvanized steel
- Available Range of Lengths: Minimum-11" Maximum-24" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable. Example: HOEB3012D5 for 12.500" length"

General

Extension Link Type	Oval-Eye Ball
Material	Steel
Strength Rating - Ultimate	30000 lb

Dimensions

Insulator Throat Diameter 0 - 0
Range

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Technical Solutions - AN-HOEB30L-SPEC-EN](#)