

Hot Line Link, Oval-Eye Oval-Eye

By ANDERSON
Catalog # [HOO30L](#)

Hot Line Chain Eye Chain Eyes are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.

Features

- Hot Line Link
- Oval Eye/Oval Eye
- UTS 30,000 lb
- Material: Body-Galvanized Forged steel
- Available Range of Lengths: L = Desired Length in 0.500" increments with minimum of 12" and maximum of 144"

General

Catalog Number	HOO30L
Extension Link Type	Oval-Eye Oval-Eye
Material	Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
----------------------------	------

Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - HOO30L](#)

