

Hot Line Link, Oval-Eye Oval-Eye

By ANDERSON
Catalog # [HOO80L](#)

"Hot Line Socket Y-Clevis, 0.750" Bent Bolt, UTS 30,000 lb"



Features

- "Material: Body-Galvanized Forged steel
- Available Range of Lengths: Minimum-14" Maximum-144" with 0.500" increment"

General

Extension Link Type	Oval-Eye Oval-Eye
Material	Steel
Strength Rating - Ultimate	80000 lb

Dimensions

Insulator Throat Diameter 0 - 0
Range

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Technical Solutions - AN-HOO80L-SPEC-EN](#)