

HUBBELL Power Systems

Hot Line Link, Oval-Eye Oval-Eye

By ANDERSON
Catalog # [HOOT50L](#)

Hot Line Chain Eye Chain Eyes are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.



Features

- Hot Line Link
- Oval Eye/Oval Eye Rotated
- UTS 50,000 lb
- Material: Body-Galvanized Forged steel
- Oval Eye/Oval Eye with one Oval Eye rotated 90 degrees
- Available Range of Lengths: L = Desired Length in 0.500" increments with minimum of 12" and maximum of 144

General

Extension Link Type	Oval-Eye Oval-Eye
Material	Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand