

Hot Line Link, Oval-Eye Eye

By ANDERSON
Catalog # [HOOT80L](#)

"Hot Line Link, Socket Eye. Eye: 1.000" Thick. With 0.813" Dia. Hole UTS 30,000 lb"



Features

- "Material: Body-Galvanized Forged steel
- Available Range of Lengths: Minimum-14" Maximum-144" with 0.500" increment"

General

Coupling Orientation	Straight
Extension Link Type	Oval-Eye Eye
Material	Ductile Iron
Strength Rating - Ultimate	30000 lb
UPC	09635940029

Dimensions

Diameter - Eye Hole	0.688 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	12 in
Weight	1.225 lb
Width - Eye	0.625 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Technical Solutions - AN-HOOT80L-SPEC-EN](#)