

Hot Line Link, Socket Eye

By ANDERSON
Catalog # [HSE100055](#)

"Hot Line Y-Clevis Clevis, Rotated, 0.750" Bent Bolt, Clevis:
1.000" Opening, 0.625" Pin, UTS 30,000 lb"



*Representative Image

Features

- "Body-Galvanized Ductile iron
- Cotter Pin-Stainless steel
- For use with ANSI class 52-3 and 52-5 insulators"

General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Series	HSE Series
Strength Rating - Ultimate	30000 lb
UPC	096359316756

Dimensions

Diameter - Eye Hole	0.688 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	10 in
Weight	2.577 lb
Width - Eye	0.688 in

Logistics

Pallet Quantity	540
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)