

**Hot Line Link, Y-Clevis Eye**

By ANDERSON  
Catalog # [HYCE301190](#)

Hot line Y-clevis eyes are used to connect associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools. The bent bolt in the Y-section provides an additional point of articulation within an assembly.

**Features**

- "Material: Body-Galvanized ductile iron, Hardware-Galvanized steel, Cotter Pin-Stainless steel
- Shield nut can be supplied by adding suffix "SN" to catalog number"

**General**

Catalog Number	HYCE301190
Coupling Orientation	Rotated
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HYCE Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359317678

**Dimensions**

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Dimensions	2.313 in x 11.938 in x 0.625 in
Height	0.625 in
Insulator Throat Diameter - Maximum	0 in



\*Representative Image

Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	2.313 in
Length - Coupling	11 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	4.655 lb
Width	11.938 in
Width - Eye	0.625 in

**Conductor Related**

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	360
-----------------	-----

**Product Assets**

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - C11713](#)  
[Specifications - HYCE301190](#)