

Hot Line Link, Y-Clevis Oval-Eye

By ANDERSON
Catalog # [HYCOE30L](#)

Hot Line Y-Clevis Oval-Eye, 0.750" Bent Bolt; Oval Eye: 0.938"
x 2.375" Opening x 0.750" Thick, UTS 30,000 lb



Features

- "Material: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: HYCOE3012D5 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Coupling Orientation	Straight
Extension Link Type	Y-Clevis Oval Eye
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Strength Rating - Ultimate	30000 lb

Dimensions

Insulator Throat Diameter Range 0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)