

Hot Line Link, Y-Clevis Oval-Eye

By ANDERSON
Catalog # [HYCOE30L90](#)

"Hexoganal Nut, Material: Aluminum alloy, Size & Thread: .500-13 , Width: 0.750"



*Representative Image

Features

- "Material: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: HYCOE3012D590 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Coupling Orientation	Rotated
Extension Link Type	Y-Clevis Oval Eye
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Strength Rating - Ultimate	30000 lb

Dimensions

Insulator Throat Diameter 0 - 0
Range

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)