

HUBBELL Power Systems

Hot Line Link, Y-Clevis Oval-Eye

By ANDERSON
Catalog # [HYCOE50L](#)

Extension Links are forged from high-strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and length required.



Features

- "Material: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: HYCOE5012D5 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Catalog Number	HYCOE50L
Coupling Orientation	Straight
Extension Link Type	Y-Clevis Oval Eye
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand