

## Connector, Parallel Groove

By ANDERSON  
Catalog # [KR1](#)

Two bolt Bronze Parallel Groove Connector



\*Representative Image

### Features

- Has conductor separator.

### General

Bolt Head Type	Hex
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318729

### Dimensions

Bolt Diameter	0.31
Diameter - Bolt	0.31 in
Weight	0.196 lb

### Conductor Related

Conductor Diameter (Tap) - Maximum	0.373 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.373
Conductor Diameter - Minimum	0.232
Conductor Diameter Range	0.232 - 0.373

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Carton Quantity	150
Pallet Quantity	7200

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - C-1363](#)

### Related Products

[KR3 - Connector, Parallel Groove](#)  
[KR4 - Connector, Parallel Groove](#)  
[KR7 - Connector, Parallel Groove](#)  
[KR2 - Connector, Parallel Groove](#)  
[KR5 - Connector, Parallel Groove](#)