

Connector, Parallel Groove

By ANDERSON
Catalog # [KR2](#)

Two bolt Bronze Parallel Groove Connector



*Representative Image

Features

- Has no cable separator.

General

Bolt Head Type	Hex
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318743

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in
Weight	0.392 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.419
Conductor Diameter - Minimum	0.26
Conductor Diameter Range	0.26 - 0.419

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	3200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - C-1363](#)

Related Products

[KR1 - Connector, Parallel Groove](#)
[KR5 - Connector, Parallel Groove](#)
[KR3 - Connector, Parallel Groove](#)
[KR6 - Connector, Parallel Groove](#)
[KR4 - Connector, Parallel Groove](#)