

Connector, Parallel Groove

By ANDERSON
Catalog # [KR3](#)



Two bolt Bronze Parallel Groove Connector

Features

Has no cable separator.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	KR3
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318767

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in

Dimensions	1.750 in x 1.125 in x 2.125 in
Height	2.125 in
Length	1.75 in
Weight	0.43 lb
Width	1.125 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.528 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.528
Conductor Diameter - Minimum	0.328
Conductor Diameter Range	0.328 - 0.528

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - C-1363](#)
- [Specifications - KR3](#)