

Connector, Parallel Groove

By ANDERSON
Catalog # [KR4](#)

Two bolt Bronze Parallel Groove Connector



*Representative Image

Features

- Has no cable separator.

General

Bolt Head Type	Hex
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318781

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Weight	0.784 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.681 in
Conductor Diameter (Tap) - Minimum	0.232 in
Conductor Diameter - Maximum	0.681
Conductor Diameter - Minimum	0.414
Conductor Diameter Range	0.414 - 0.681

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - C-1363](#)

Related Products

[KR3 - Connector, Parallel Groove](#)
[KR6 - Connector, Parallel Groove](#)
[KR7 - Connector, Parallel Groove](#)
[KR2 - Connector, Parallel Groove](#)
[KR5 - Connector, Parallel Groove](#)