

Connector, Parallel Groove

By ANDERSON
Catalog # [KR6](#)

Two bolt Bronze Parallel Groove Connector



*Representative Image

Features

Has no cable separator.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	KR6
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318828

Dimensions

Bolt Diameter	0.5
---------------	-----

Diameter - Bolt	0.5 in
Weight	1.274 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	1.031 in
Conductor Diameter (Tap) - Minimum	0.292 in
Conductor Diameter - Maximum	1.031
Conductor Diameter - Minimum	0.675
Conductor Diameter Range	0.675 - 1.031

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - C-1363](#)
- [Specifications - KR6](#)