

Coupler, Bronze Bolted

By ANDERSON
Catalog # [L900606](#)

"Coupler, Tube to Cable, Bronze Bolted, 3/4" IPS tube to 0.325"-0.813" dia. cable, Material: Castings-Bronze alloy, Hardware-silicon bronze or stainless steel"



*Representative Image

Features

- "Hex Stops on the casting allows for one-wrench installation"

General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Type	Tube to Cable Couplers
UPC	096359475880

Dimensions

Diameter - Clamping Hardware	0.50 in
Diameter - Rod / Tube	3/4 in
Weight	3.528 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
---	-----------------------

Conductor Related

Conductor Type	Copper Bus
----------------	------------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4084 \(L45 and L90 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)