

Arrester Terminal Connector

By ANDERSON
Catalog # [LAT20](#)



*Representative Image

Features

2 position eyebolt allows parallel or perpendicular conductor installation.

General

Bolt Installation Torque (Recommended)	240 ft-lbs
Catalog Number	LAT20
Cover Available	No
Inhibitor Loaded	No
Material	Bronze; Copper
Material - Body	Bronze Alloy
Material - Eyebolt	Silicon Bronze
Material - Hardware	Silicon Bronze or Stainless Steel
Number of Stud Threads	16
Plating	No
Product Category	Mechanical Connectors
Style	2 Position Eye Bolt
UPC	096359319351

Dimensions

Bolt Diameter	0.38 in
Diameter - Bolt	0.38 in
Diameter - Stud	0.375 in

Dimensions	1.690 in x 1.250 in x 1.880 in
Height	1.88 in
Length	1.69 in
Weight	0.392 lb
Width	1.25 in

Conductor Related

Conductor Diameter - Maximum	0.42 in
Conductor Diameter - Minimum	0.12 in
Conductor Diameter Range	0.12 - 0.420

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Carton Quantity	50
Pallet Quantity	3200

Product Assets

[Catalogs - Distribution Connectors](#)
[Specifications - LAT20](#)