

Connector, Parallel Groove

By ANDERSON
Catalog # [LC1004](#)

Single U-Bolt Bronze Parallel Groove Connector



*Representative Image

Features

For copper to copper conductor connectors

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LC1004
Cover Available	No
EU RoHS Indicator	No
Material	Bronze
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Single U-Bolt
UPC	096359319405

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in

Dimensions	2.000 in x 2.437 in x 3.500 in
Height	3.5 in
Length	2 in
Weight	1.2 lb
Width	2.437 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.63 in
Conductor Diameter (Tap) - Minimum	0.325 in
Conductor Diameter - Maximum	0.63
Conductor Diameter - Minimum	0.325
Conductor Diameter Range	0.325 - 0.63
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	1800
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Specifications - LC1004](#)