

HUBBELL Power Systems

Connector, Parallel Groove

By ANDERSON
Catalog # [LC1133](#)

Two U-Bolt Bronze Parallel Groove Connector



*Representative Image

Features

For copper to copper conductor connectors

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LC1133
Cover Available	No
EU RoHS Indicator	No
Material	Bronze
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359319429

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in
Dimensions	2.750 in x 1.937 in x 3.000 in
Height	3 in
Length	2.75 in
Weight	1.568 lb
Width	1.937 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.528 in
Conductor Diameter (Tap) - Minimum	0.289 in
Conductor Diameter - Maximum	0.528
Conductor Diameter - Minimum	0.289
Conductor Diameter Range	0.289 - 0.528
Conductor Type	Copper

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - C-2811](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-LC1133-SPEC-EN | REV 6/2024