

Connector, Parallel Groove

By ANDERSON  
Catalog # [LC1155](#)

Two U-Bolt Bronze Parallel Groove Connector



\*Representative Image

Features

For copper to copper conductor connectors

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LC1155
Cover Available	No
EU RoHS Indicator	No
Material	Bronze
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359319467

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in

Dimensions	3.375 in x 2.937 in x 4.000 in
Height	4 in
Length	3.375 in
Weight	2.352 lb
Width	2.937 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.813 in
Conductor Diameter (Tap) - Minimum	0.46 in
Conductor Diameter - Maximum	0.813
Conductor Diameter - Minimum	0.46
Conductor Diameter Range	0.46 - 0.813
Conductor Type	Copper

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - C-2811](#)
- [Specifications - LC1155](#)