

HUBBELL Power Systems

Connector, Parallel Groove

By ANDERSON
Catalog # [LC1177](#)

Two U-Bolt Bronze Parallel Groove Connector



*Representative Image

Features

For copper to copper conductor connectors

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LC1177
Cover Available	No
EU RoHS Indicator	No
Material	Bronze
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359319481

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Dimensions	4.000 in x 3.062 in x 5.000 in
Height	5 in
Length	4 in
Weight	3.528 lb
Width	3.062 in

Conductor Related

Conductor Diameter (Tap) - Maximum	1.152 in
Conductor Diameter (Tap) - Minimum	0.811 in
Conductor Diameter - Maximum	1.152
Conductor Diameter - Minimum	0.813
Conductor Diameter Range	0.813 - 1.152
Conductor Type	Copper

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - C-2811](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-LC1177-SPEC-EN | REV 6/2024