

Connector, Parallel Groove

By ANDERSON
Catalog # [LC402](#)



*Representative Image

Two Center Bolt Bronze Parallel Groove Connector

Features

For copper to copper conductor connectors

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LC402
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two Center Bolts
UPC	096359319528

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in
Dimensions	2.281 in x 1.843 in x 2.250 in
Height	2.25 in
Length	2.281 in
Weight	0.784 lb

Width	1.843 in
-------	----------

Conductor Related

Conductor Diameter (Main) - Maximum	0.528 in
Conductor Diameter (Main) - Minimum	0.204 in
Conductor Diameter (Main) Range	0.204 - 0.528
Conductor Diameter (Tap) - Maximum	0.528 in
Conductor Diameter (Tap) - Minimum	0.204 in
Conductor Diameter - Maximum	0.528
Conductor Diameter - Minimum	0.204
Conductor Diameter Range	0.204 - 0.528
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Logistics

Pallet Quantity	1500
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Specifications - LC402](#)