

Compression Splice Partial Tension

By ANDERSON
Catalog # [PTA10](#)



Partial Tension Aluminum splice for 1/0 (7 and 19 strand) AAC.

*Representative Image

Features

Meets ANSI C119.4 requirements for partial tension.

General

Catalog Number	PTA10
Compression Method	VersaCrimp or Conventional
Die Tooling	BG, 243
Die Index	BG, 243
Die Size	<ul style="list-style-type: none">VC6 (all)Kearney 5/8, 5/8-1T&B 52EEI 8A
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359324072

Dimensions

Length Before Compression	3.25 in
Weight	0.098 lb
Conductor Related	
Conductor Compatibility	AAC-Poppy-1/0-7
Conductor Diameter - Maximum	0.373
Conductor Diameter - Minimum	0.336
Conductor Diameter Range	0.336 - 0.373

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - CC-215E](#)
- [Specifications - PTA10](#)