

HUBBELL

Power Systems

Compression Splice Partial Tension

By ANDERSON
Catalog # [PTA795](#)

Partial Tension Aluminum splice for 750 - 800 (37 and 61) strand AAC.



*Representative Image

Features

Meets ANSI C119.4 requirements for partial tension.

General

Catalog Number	PTA795
Compression Method	VersaCrimp or Conventional
Die Index	342
Die Size	VC8
	Kearney 1-5/8
	T&B140
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359356660

Dimensions

Length Before Compression	10.5 in
Weight	1.47 lb

Conductor Related

Conductor Compatibility	AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Snapdragon-900-61
Conductor Diameter - Maximum	1.031
Conductor Diameter - Minimum	0.998
Conductor Diameter Range	0.998 - 1.031

Certifications And Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - CC-215E](#)



A Hubbell brand