

Hot Line Tap Clamp, Aluminum

By ANDERSON
Catalog # [S1520AA](#)

Overhead Primary Tap, Hot Line Tap Clamp, Aluminum, AAC|AAAC|ACSR, Range 0.128 - 0.419 in



*Representative Image

Features

- High pressure developed by eyestem, lock washer assures permanent connection.

General

Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Eyebolt	Tin Plated Bronze
Material - Eyestem	Forged Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359054023

Dimensions

Weight	0.392 lb
--------	----------

Electrical Ratings

Maximum Current Rating Amps Continuous	Rated for maximum rating of largest tap conductor in range
---	---

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.128
Conductor Diameter Range	0.128 - 0.419

Logistics

Packaging Type	Box
Pallet Quantity	3600

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)

Related Products

- [AH4 - Hot Line Tap Clamp, Aluminum](#)
- [S1530AA - Hot Line Tap Clamp, Aluminum](#)
- [S1540AA - Hot Line Tap Clamp, Aluminum](#)
- [S1534AGP - Hot Line Tap Clamp, Aluminum, Tin Plated](#)