

Hot Line Tap Clamp, Aluminum

By ANDERSON
Catalog # [S1530AA](#)

Overhead Primary Tap, Hot Line Tap Clamp, Aluminum,
AAC|AAAC|ACSR, Range 0.162 - 0.743 in



*Representative Image

Features

High pressure developed by eyestem, lock washer assures permanent connection.

General

Catalog Number	S1530AA
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Eyebolt	Tin Plated Bronze
Material - Eyestem	Forged Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359054078

Dimensions

Dimensions	2.400 in x 2.400 in x 7.130 in
Height	7.13 in
Length	2.4 in
Weight	0.627 lb
Width	2.4 in

Electrical Ratings

Maximum Current Rating Amps Continuous	Rated for maximum rating of largest tap conductor in range
--	--

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-
-------------------------	--

26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

Conductor Diameter (Tap) - Maximum	0.743 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.743 in
Conductor Diameter - Minimum	0.162
Conductor Diameter Range	0.162 - 0.743

Logistics

Packaging Type	Box
----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - CC-25767](#)
- [Specifications - S1530AA](#)